



# Compression Splice Reducer

By Burndy  
Catalog # [YSR3125FXLTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil, Barrel B 1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C), Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Red/Pink Color Code, 18/12 Die Index.



## Application

Wire Reducing Splice

## General

Color Code	Red, Pink
Color Code - Side A	Red
Color Code - Side B	Pink
Connector Type	STANDARD BARREL KITS
Die Index	18/12
Die Index - Element A	18
Die Index - Element B	12
Die Index Run Side	18
Die Index Tap Side	12
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810345337
UPC 12 Digit	7818103453377

## Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.49 in
Dimension - L Length Overall mm	85 mm
Dimension - Length BB inch	1.04 in
Dimension - Length Overall inch	3.33 in
Dimension - Strip Length inch	1.41 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Size B	1/0 AWG
Conductor - Copper Flex G Tap	1/0 AWG
Conductor - Copper Flex H Size B	1/0 AWG
Conductor - Copper Flex H Tap	1/0 AWG
Conductor - Copper Flex I Size B	1/0 AWG
Conductor - Copper Flex I Tap	1/0 AWG
Conductor - Copper Flex K Size B	1/0 AWG
Conductor - Copper Flex K Tap	1/0 AWG
Conductor - Copper Flex M Size B	1/0 AWG
Conductor - Copper Flex M Tap	1/0 AWG
Conductor - Copper Str Size	350 KCMIL-1/0 AWG
Conductor - Copper Str Size A	350 kcmil
Conductor - Material	COPPER
Conductor Size	350 KCMIL-1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	350 KCMIL-1/0 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1728

## Product Assets

- [3D Models - YSR3125FXLTCKITC\\_MODEL-PDF](#)
- [3D Models - YSR3125FXLTCKITC\\_MODEL-STEP](#)
- [3D Models - YSR3125FXLTCKITC\\_MODEL-IGES](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YSR3125FXLTCKITC-SPEC-EN | REV 8/2023