



Compression Splice Reducer

By Burndy
 Catalog # YSR32FX28FXLTCKITC

CU Splice Reducer, Barrel A 300 kcmil G,H,I,K,M,313 DLO, Barrel B 4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Red/Purple Color Code, 18/15 Die Index.



Application

Wire Reducing Splice

General

Color Code	Blue, Purple
Color Code - Side A	Red
Color Code - Side B	Purple
Connector Type	STANDARD BARREL KITS
Die Index	18/15
Die Index - Element A	19;L80
Die Index - Element B	15
Die Index Run Side	19;L80
Die Index Tap Side	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810345207
UPC 12 Digit	7818103452077

Dimensions

Dimension - B Length fraction	1-9/16 in
Dimension - B Length inch	1.57 in
Dimension - L Length Overall mm	88 mm
Dimension - Length BB inch	1.43 in
Dimension - Length Overall inch	3.46 in
Dimension - Strip Length inch	1.48 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	300 KCMIL
Conductor - Copper Flex G Size A	300 kcmil
Conductor - Copper Flex G Size A Range	300 kcmil
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex H Run	300 KCMIL
Conductor - Copper Flex H Size A	300 kcmil
Conductor - Copper Flex H Size A Range	300 kcmil
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	300 KCMIL
Conductor - Copper Flex I Size A	300 kcmil
Conductor - Copper Flex I Size A Range	300 kcmil
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	300 KCMIL
Conductor - Copper Flex K Size A	300 kcmil
Conductor - Copper Flex K Size A Range	300 kcmil
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex M Run	300 KCMIL
Conductor - Copper Flex M Size A	300 kcmil
Conductor - Copper Flex M Size A Range	300 kcmil
Conductor - Copper Flex M Tap	4/0 AWG
Conductor - Copper Str Size	300 KCMIL-4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	300 KCMIL-4/0 AWG
Conductor Type	CODE/FLEX
Wire Size	300 KCMIL-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2250

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSR32FX28FXLTCKITC-SPEC-EN | REV 8/2023