



YSR34FX29FXLTCKITC, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 250 kcmil, includes clear heat shrink

By Burndy

Catalog # [YSR34FX29FXLTCKITC](#)



CU Splice Reducer, Barrel A 350 kcmil G,H,I,K,M,373 DLO, Barrel B 250 kcmil, 4/0 G,H,I,K,M,DLO, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Blue/Yellow Color Code, 19 or L80/16 Die Index.

Application

Wire Reducing Splice

General

Catalog Number	YSR34FX29FXLTCKITC
Color Code	Blue, Yellow
Color Code - Side A	Blue
Color Code - Side B	Yellow
Connector Type	STANDARD BARREL KITS
Die Index	19/16
Die Index - Element A	19;L80
Die Index - Element B	16
Die Index Run Side	19;L80
Die Index Tap Side	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810472354
UPC 12 Digit	7818104723544

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - L Length Overall mm	97 mm
Dimension - Length BB inch	1.44 in
Dimension - Length Overall inch	3.81 in
Dimension - Strip Length inch	1.60 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex G Size	350 kcmil
A	
Conductor - Copper Flex G Size	350 kcmil
A Range	
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex H Run	350 KCMIL
Conductor - Copper Flex H Size	350 kcmil
A	
Conductor - Copper Flex H Size	350 kcmil
A Range	
Conductor - Copper Flex H Size	N/A
B Range	
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Flex I Size	350 kcmil
A	
Conductor - Copper Flex I Size	350 kcmil
A Range	
Conductor - Copper Flex I Size	4/0 AWG
B	
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex K Size	350 kcmil
A	
Conductor - Copper Flex K Size	350 kcmil
A Range	
Conductor - Copper Flex K Size	4/0 AWG
B	
Conductor - Copper Flex K Size	4/0 AWG
B Range	
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex M Run	350 KCMIL
Conductor - Copper Flex M	350 kcmil
Size A	
Conductor - Copper Flex M	350 kcmil
Size A Range	
Conductor - Copper Flex M	4/0 AWG
Size B	
Conductor - Copper Flex M	4/0 AWG
Size B Range	
Conductor - Copper Flex M Tap	4/0 AWG
Conductor - Copper Str Size	350 KCMIL-250 KCMIL
Conductor - Material	COPPER
Conductor Size	350 KCMIL-250 KCMIL
Conductor Type	CODE/FLEX
Wire Size	350 KCMIL-250 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	864

Product Assets

[3D Models - YSR34FX29FXLTCKITC_MODEL-PDF](#)
[3D Models - YSR34FX29FXLTCKITC_MODEL-IGES](#)
[3D Models - YSR34FX29FXLTCKITC_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10021428](#)
[Specifications - YSR34FX29FXLTCKITC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YSR34FX29FXLTCKITC-SPEC-EN | REV 8/2024