



# Compression Splice Reducer

By Burndy  
Catalog # YSR34FX29FXTEL24

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:350 kcmil(Flex-Str) Barrel B:4/O AWG(Flex-Str), Standard Barrel, Electro-Tin Plated.



## Application

Wire Reducing Splice

## General

Color Code	Blue, Yellow
Color Code - Side A	Blue
Color Code - Side B	Yellow
Connector Type	STANDARD BARREL KITS
Die Index	19/16
Die Index Run Side	19;L80
Die Index Tap Side	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810345054
UPC 12 Digit	7818103450544

## Dimensions

Dimension - B Length fraction	2-3/4 in
Dimension - B Length inch	2.75 in
Dimension - L Length Overall mm	147 mm
Dimension - Length BB inch	2.36 in
Dimension - Length Overall inch	5.78 in
Dimension - Strip Length inch	2.67 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex G Size A	350 kcmil
Conductor - Copper Flex G Size A Range	350 kcmil
Conductor - Copper Flex G Size B Range	4/O AWG
Conductor - Copper Flex G Tap	4/O AWG
Conductor - Copper Flex H Run	350 KCMIL
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex H Size A Range	350 kcmil
Conductor - Copper Flex H Size B Range	4/O AWG
Conductor - Copper Flex H Tap	4/O AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Flex I Size A	350 kcmil
Conductor - Copper Flex I Size A Range	350 kcmil
Conductor - Copper Flex I Size B	4/O AWG
Conductor - Copper Flex I Size B Range	4/O AWG
Conductor - Copper Flex I Tap	4/O AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size A Range	350 kcmil
Conductor - Copper Flex K Size B	4/O AWG
Conductor - Copper Flex K Size B Range	4/O AWG
Conductor - Copper Flex K Tap	4/O AWG
Conductor - Copper Flex M Run	350 KCMIL
Conductor - Copper Flex M Size A	350 kcmil
Conductor - Copper Flex M	350 kcmil

Size A Range	
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Flex M Size B Range	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor - Copper Str Size	350 KCMIL-250 KCMIL
Conductor - Copper Str Size B	4/0 AWG
Conductor - Material	COPPER
Conductor Size	350 KCMIL-250 KCMIL
Conductor Type	CODE/FLEX
Wire Size	350 KCMIL-250 KCMIL

### **Certifications And Compliance**

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### **Logistics**

Carton Quantity	6
Minimum Pack Quantity	6
Pallet Quantity	540

### **Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - SPLICE KIT trilingual](#)  
[Sales Drawings - 10101352](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YSR34FX29FXTEL24-SPEC-EN | REV 5/2024