



Compression Splice Reducer

By Burndy
Catalog # [YSR34FX2CFXLTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil G,H,I,K,M,373 DLO, Barrel B 2 Flex G,H,I,K,M,DLO, 2 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Blue/Brown Color Code, 19 or L80/10 Die Index.



Application

Wire Reducing Splice

General

Color Code	Blue, Brown
Color Code - Side A	Blue
Color Code - Side B	Brown
Connector Type	STANDARD BARREL KITS
Die Index	19/10
Die Index - Element A	19;L80
Die Index - Element B	10
Die Index Run Side	19;L80
Die Index Tap Side	10
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810473870
UPC 12 Digit	7818104738700

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - L Length Overall mm	102 mm
Dimension - Length BB inch	0.82 in
Dimension - Length Overall inch	4.02 in
Dimension - Strip Length inch	1.60 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex G Size A	350 kcmil
Conductor - Copper Flex G Size A Range	350 kcmil
Conductor - Copper Flex G Size B Range	2 AWG
Conductor - Copper Flex G Tap	2 AWG
Conductor - Copper Flex H Run	350 KCMIL
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex H Size A Range	350 kcmil
Conductor - Copper Flex H Size B Range	2 AWG
Conductor - Copper Flex H Tap	2 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Flex I Size A	350 kcmil
Conductor - Copper Flex I Size A Range	350 kcmil
Conductor - Copper Flex I Size B	2 AWG
Conductor - Copper Flex I Size B Range	2 AWG
Conductor - Copper Flex I Tap	2 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size A Range	350 kcmil
Conductor - Copper Flex K Size B	2 AWG
Conductor - Copper Flex K Size B Range	2 AWG
Conductor - Copper Flex K Tap	2 AWG
Conductor - Copper Flex M Run	350 KCMIL
Conductor - Copper Flex M Size A	350 kcmil
Conductor - Copper Flex M	350 kcmil

Size A Range	
Conductor - Copper Flex M Size B	2 AWG
Conductor - Copper Flex M Size B Range	2 AWG
Conductor - Copper Flex M Tap	2 AWG
Conductor - Copper Str Size	350 KCMIL-2 AWG
Conductor - Copper Str Size B	2 AWG
Conductor - Material	COPPER
Conductor Size	350 KCMIL-2 AWG
Conductor Type	CODE/FLEX
Wire Size	350 KCMIL-2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	900

Product Assets

[3D Models - YSR34FX2CFXLTCKITC_MODEL-PDF](#)
[3D Models - YSR34FX2CFXLTCKITC_MODEL-STEP](#)
[3D Models - YSR34FX2CFXLTCKITC_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSR34FX2CFXLTCKITC-SPEC-EN | REV 5/2024