



Compression Splice Reducer

By Burndy
 Catalog # YSR38FX34FXLTCKITC

CU Splice Reducer, Barrel A 500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO, Barrel B 350 kcmil G,H,I,K,M,373 DLO, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Pink/Blue Color Code, L99/19 or L80 Die Index.



Application

Wire Reducing Splice

General

Color Code	Pink, Blue
Color Code - Side A	Pink
Color Code - Side B	Blue
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	L99/19
Die Index - Element A	L99
Die Index - Element B	19;L80
Die Index Run Side	L99
Die Index Tap Side	19;L80
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYREDUCER
Temperature Rating	194
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810472323
UPC 12 Digit	7818104723233

Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - L Length Overall mm	103 mm
Dimension - Length BB inch	1.69 in
Dimension - Length Overall inch	4.06 in
Dimension - Strip Length inch	1.77 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	500-550 KCMIL
-------------------------------	---------------

Size B

Conductor - Copper Flex H Size B Range	350 kcmil
Conductor - Copper Flex H Tap	350 KCMIL
Conductor - Copper Flex H Tap Range	350 kcmil
Conductor - Copper Flex I Run Size A	500-550 KCMIL
Conductor - Copper Flex I Size A Range	500 kcmil
Conductor - Copper Flex I Size B	350 kcmil
Conductor - Copper Flex I Size B Range	350 kcmil
Conductor - Copper Flex I Tap	350 KCMIL
Conductor - Copper Flex K Run	500-550 KCMIL
Conductor - Copper Flex K Size A	500 kcmil
Conductor - Copper Flex K Size A Range	500 kcmil
Conductor - Copper Flex K Size B	350 kcmil
Conductor - Copper Flex K Size B Range	350 kcmil
Conductor - Copper Flex K Tap	350 KCMIL
Conductor - Copper Flex M Run	500-550 KCMIL
Conductor - Copper Flex M Size A	500 kcmil
Conductor - Copper Flex M Size A Range	500 kcmil
Conductor - Copper Flex M Size B	350 kcmil
Conductor - Copper Flex M Size B Range	350 kcmil
Conductor - Copper Flex M Tap	350 KCMIL
Conductor - Copper Str Size	500KCMIL-550 KCMIL-350 KCMIL
Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Str Size B Range	350 kcmil
Conductor - Material	COPPER
Conductor Size	500KCMIL-550 KCMIL-350

Conductor - Copper Flex G Run Range	500 kcmil
Conductor - Copper Flex G Size A	500 kcmil
Conductor - Copper Flex G Size A Range	500 kcmil
Conductor - Copper Flex G Size B	350 kcmil
Conductor - Copper Flex G Size B Range	350 kcmil
Conductor - Copper Flex G Tap	350 KCMIL
Conductor - Copper Flex G Tap Range	350 kcmil
Conductor - Copper Flex H Run	500-550 KCMIL
Conductor - Copper Flex H Run Range	500 kcmil
Conductor - Copper Flex H Size A	500 kcmil
Conductor - Copper Flex H Size A Range	500 kcmil
Conductor - Copper Flex H	350 kcmil

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

Product Assets

- [3D Models - YSR38FX34FXLTCKITC_MODEL-IGES](#)
- [3D Models - YSR38FX34FXLTCKITC_MODEL-STEP](#)
- [3D Models - YSR38FX34FXLTCKITC_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Sales Drawings - 10021428](#)

Conductor Size	500KCMIL-550 KCMIL-350 KCMIL
Conductor Type	FLEX
Wire Size	500KCMIL-550 KCMIL-350 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No



A proud member of the Hubbell Family.