



Compression Splice Reducer

By Burndy
Catalog # YSR3928LTCKITC

CU Splice Reducer, Barrel A 750 kcmil, Barrel B 4/0 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Black/Purple Color Code, 24/15 Die Index.



Application

Wire Reducing Splice

General

Color Code	Black, Purple
Color Code - Side A	Black
Color Code - Side B	Purple
Connector Type	STANDARD BARREL KITS
Die Index	24/15
Die Index - Element A	24
Die Index - Element B	15
Die Index Run Side	24
Die Index Tap Side	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810344606
UPC 12 Digit	7818103446066

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.78 in
Dimension - L Length Overall mm	118 mm
Dimension - Length BB inch	1.30 in
Dimension - Length Overall inch	4.65 in
Dimension - Strip Length inch	1.67 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	750 KCMIL-4/0 AWG
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	750 KCMIL-4/0 AWG
Conductor Type	CODE
Wire Size	750 KCMIL-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - YSR3928LTCKITC_MODEL-IGES](#)
- [3D Models - YSR3928LTCKITC_MODEL-PDF](#)
- [3D Models - YSR3928LTCKITC_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

