



YSR3929FXLTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 250 kcmil, includes clear heat shrink

By Burndy
Catalog # YSR3929FXLTCKITC



CU Splice Reducer, Barrel A 750 kcmil, Barrel B 250 kcmil, 4/0 G,H,I,K,M,DLO, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Black/Yellow Color Code, 24/16 Die Index.

Application

Wire Reducing Splice

General

Catalog Number	YSR3929FXLTCKITC
Color Code	Black, Yellow
Color Code - Side A	Black
Color Code - Side B	Yellow
Connector Type	STANDARD BARREL KITS
Die Index	24/16
Die Index - Element A	24
Die Index - Element B	16
Die Index Run Side	24
Die Index Tap Side	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810472316
UPC 12 Digit	7818104723166

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.78 in
Dimension - L Length Overall mm	117 mm
Dimension - Length BB inch	1.44 in
Dimension - Length Overall inch	4.59 in
Dimension - Strip Length inch	1.67 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex K Size B Range	4/0 AWG
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Flex M Size B Range	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor - Copper Str Size	750 KCMIL-250 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL-250 KCMIL
Conductor Type	CODE/FLEX
Wire Size	750 KCMIL-250 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	864

Product Assets

3D Models - YSR3929FXLTCKITC_MODEL-IGES

3D Models - YSR3929FXLTCKITC_MODEL-STEP

3D Models - YSR3929FXLTCKITC_MODEL-PDF

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section C - Compression

Connections

Customer Notices - Prop 65 Notice

Installation Manuals - SPLICE KIT trilingual

Interactive Catalog - BURNDY Full-Line Digital Catalog

Sales Drawings - 10021428

Specifications - YSR3929FXLTCKITC



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSR3929FXLTCKITC-SPEC-EN | REV 8/2024