



Compression Splice Reducer

By Burndy
Catalog # [YSR3939LTCKITC](#)

CU Splice Reducer, Barrel A 750 kcmil, Barrel B 750 kcmil, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Black/Black Color Code, 24/24 Die Index.



Application

Wire Reducing Splice

General

Color Code	Black, Black
Color Code - Side A	Black
Color Code - Side B	Black
Connector Type	STANDARD BARREL KITS
Die Index	24/24
Die Index - Element A	24
Die Index - Element B	24
Die Index Run Side	24
Die Index Tap Side	24
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810491041
UPC 12 Digit	7818104910411

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.78 in
Dimension - L Length Overall mm	105 mm
Dimension - Length BB inch	1.78 in
Dimension - Length Overall inch	4.13 in
Dimension - Strip Length inch	1.67 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	750 KCMIL-750 KCMIL
Conductor - Copper Str Size B	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL-750 KCMIL
Conductor Type	CODE
Wire Size	750 KCMIL-750 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSR3939LTCKITC-SPEC-EN | REV 8/2023