



Compression Splice Reducer

By Burndy
Catalog # YSR44FX30LTCKITC

CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 300 kcmil, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Yellow/White Color Code, L115/17 or 298 Die Index.



Application

Wire Reducing Splice

General

Color Code	Yellow, White
Color Code - Side A	Yellow
Color Code - Side B	White
Connector Type	STANDARD BARREL KITS
Die Index	L115/17
Die Index - Element A	L115
Die Index - Element B	17;298
Die Index Run Side	L115
Die Index Tap Side	17;298
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810491065
UPC 12 Digit	7818104910655

Dimensions

Dimension - B Length fraction	2-1/16 in
Dimension - B Length inch	2.09 in
Dimension - L Length Overall mm	127 mm
Dimension - Length BB inch	1.30 in
Dimension - Length Overall inch	5.01 in
Dimension - Strip Length inch	1.96 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex H Run	750 KCMIL
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Flex I Size A	750 KCMIL
Conductor - Copper Flex I Size A Range	750 KCMIL
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex M Run	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Str Size	750 KCMIL-300 KCMIL
Conductor - Copper Str Size B	300 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL-300 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL-300 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSR44FX30LTCKITC-SPEC-EN | REV 8/2023