



YSR44FX31LTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 350 kcmil, includes clear heat shrink

By Burndy
Catalog # YSR44FX31LTCKITC



CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 350 kcmil, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Yellow/Red Color Code, L115/18 Die Index.

Application

Wire Reducing Splice

General

Catalog Number	YSR44FX31LTCKITC
Color Code	Yellow, Red
Color Code - Side A	Yellow
Color Code - Side B	Red
Connector Type	STANDARD BARREL KITS
Die Index	L115/18
Die Index - Element A	L115
Die Index - Element B	18
Die Index Run Side	L115
Die Index Tap Side	18
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810344354
UPC 12 Digit	7818103443544

Dimensions

Dimension - B Length fraction	2-1/16 in
Dimension - B Length inch	2.09 in
Dimension - L Length Overall mm	132 mm
Dimension - Length BB inch	1.49 in
Dimension - Length Overall inch	5.18 in
Dimension - Strip Length inch	1.96 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Flex G Size	750 kcmil A
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex H Run	750 KCMIL
Conductor - Copper Flex H Size	750 kcmil A
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Flex I Size	750 KCMIL A
Conductor - Copper Flex I Size A Range	750 KCMIL
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex K Size	750 KCMIL A
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex M Run	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Str Size	750 KCMIL-300 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Str Size B Range	350 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL-300 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL-300 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	6
Pallet Quantity	540

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10021428](#)
[Specifications - YSR44FX31LTCKITC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YSR44FX31LTCKITC-SPEC-EN | REV 8/2024