



## YSR44FX38FXLTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 500 kcmil, includes clear heat shrink

By Burndy

Catalog # [YSR44FX38FXLTCKITC](#)



CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Yellow/Pink Color Code, L115/L99 Die Index.

### Application

Wire Reducing Splice

### General

Catalog Number	YSR44FX38FXLTCKITC
Color Code	Yellow, Pink
Color Code - Side A	Yellow
Color Code - Side B	Pink
Connector Type	STANDARD BARREL KITS
Die Index	L115/L99
Die Index - Element A	L115
Die Index - Element B	L99
Die Index Run Side	L115
Die Index Tap Side	L99
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810472279
UPC 12 Digit	7818104722799

### Dimensions

Dimension - B Length fraction	2-1/16 in
Dimension - B Length inch	2.09 in
Dimension - L Length Overall mm	117 mm
Dimension - Length BB inch	1.60 in
Dimension - Length Overall inch	4.61 in
Dimension - Strip Length inch	1.96 in

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex G Size B	500 kcmil
Conductor - Copper Flex G Size B Range	500 kcmil
Conductor - Copper Flex G Tap	500-550 KCMIL
Conductor - Copper Flex H Run	750 KCMIL
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex H Size B	350 kcmil
Conductor - Copper Flex H Size B Range	500 kcmil
Conductor - Copper Flex H Tap	500-550 KCMIL
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Flex I Size A	750 KCMIL
Conductor - Copper Flex I Size A Range	750 KCMIL
Conductor - Copper Flex I Size B	500 kcmil
Conductor - Copper Flex I Size B Range	500 kcmil
Conductor - Copper Flex I Tap	500-550 KCMIL
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex K Size B	500 kcmil
Conductor - Copper Flex K Size B Range	500 kcmil
Conductor - Copper Flex K Tap	500-550 KCMIL
Conductor - Copper Flex M Run	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Flex M Size B	500 kcmil
Conductor - Copper Flex M Size B Range	500 kcmil
Conductor - Copper Flex M Tap	500-550 KCMIL
Conductor - Copper Str Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Str Size B	500 kcmil
Conductor - Copper Str Size B Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL-500 KCMIL-550 KCMIL

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	864

## Product Assets

[3D Models - YSR44FX38FXLTCKITC\\_MODEL-STEP](#)  
[3D Models - YSR44FX38FXLTCKITC\\_MODEL-IGES](#)  
[3D Models - YSR44FX38FXLTCKITC\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - SPLICE KIT trilingual](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10021428](#)  
[Specifications - YSR44FX38FXLTCKITC](#)



A Hubbell brand