



YSR4CFX10CLTCKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 4 Flex/AWG, Barrel B: 14-10 AWG

By Burndy
Catalog # YSR4CFX10CLTCKITC



CU Splice Reducer, Barrel A 4 Flex G,H,I,K,M,DLO, 4 AWG, Barrel B 1410 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Gray Color Code, 8 Die Index.

Application

Wire Reducing Splice

General

Color Code	Gray
Color Code - Side A	Gray
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	8
Die Index - Element A	8
Die Index Run Side	8
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYREDUCER
Temperature Rating	194
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810473955
UPC 12 Digit	7818104739555

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.74 in
Dimension - L Length Overall mm	42 mm
Dimension - Length BB inch	0.66 in
Dimension - Length Overall inch	1.66 in
Dimension - Strip Length inch	0.71 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Run	4 AWG

Size A

Conductor - Copper Flex I Size A Range	4 AWG
Conductor - Copper Flex I Size B	10 AWG
Conductor - Copper Flex I Size B Range	10 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Run	4 AWG
Conductor - Copper Flex K Size A	4 AWG
Conductor - Copper Flex K Size A Range	4 AWG
Conductor - Copper Flex K Size B	10 AWG
Conductor - Copper Flex K Size B Range	10 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Run	4 AWG
Conductor - Copper Flex M Size A	4 AWG
Conductor - Copper Flex M Size A Range	4 AWG
Conductor - Copper Flex M Size B	10 AWG
Conductor - Copper Flex M Size B Range	10 AWG
Conductor - Copper Solid Size B	12;11;10
Conductor - Copper Str Run Range	4 AWG
Conductor - Copper Str Size	4 AWG-10 AWG
Conductor - Copper Str Size B	10 AWG
Conductor - Copper Str Tap Range	14-10 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG-10 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG-10 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No

Conductor - Copper Flex G Size A	4 AWG
Conductor - Copper Flex G Size A Range	4 AWG
Conductor - Copper Flex G Size B	10 AWG
Conductor - Copper Flex G Size B Range	10 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Run	4 AWG
Conductor - Copper Flex H Size A	4 AWG
Conductor - Copper Flex H Size A Range	4 AWG
Conductor - Copper Flex H Size B	10 AWG
Conductor - Copper Flex H Size B Range	10 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Run	4 AWG
Conductor - Copper Flex I	4 AWG

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	6000

Product Assets

- [3D Models - YSR4CFX10CLTCKITC_MODEL-STEP](#)
- [3D Models - YSR4CFX10CLTCKITC_MODEL-PDF](#)
- [3D Models - YSR4CFX10CLTCKITC_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSR4CFX10CLTCKITC-SPEC-EN | REV 5/2024