

## YSS2R, Single Aluminum Sleeve

By Burndy  
Catalog # [YSS2R](#)



Single aluminum sleeve designed for service drop or short span overhead distribution lines, Die index: BG or 5/8.

### Application

For Aluminum, ACSR, 6201, 5005 And Compressed Conductors And Service Drop Or Short Span Overhead Distribution Lines

### General

Catalog Number	YSS2R
Color Code	Red
Connector Type	Splice
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YSS
UPC	781810169551
UPC 12 Digit	7818101695511

### Dimensions

Dimension - B Length fraction	1-39/50 in
Dimension - B Length inch	1.78 in
Dimension - L Length Overall mm	96 mm
Dimension - Length Overall inch	3.78 in
Dimension - Outside Diameter inch	0.65 in

### Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	14800

### Product Assets

- [3D Models - YSS2R\\_MODEL-PDF](#)
- [3D Models - YSS2R\\_MODEL-STEP](#)
- [3D Models - YSS2R\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YSS\\_LineArt](#)
- [Sales Drawings - sc031169-01](#)
- [Specifications - YSS2R](#)