



Compresson T-Connector

By Burndy
Catalog # YSTICICT



UNINSULATED HIGH VOLTAGE COPPER COMPRESSION
SPLICE STANDARD BARREL-TAPERED ENDS.

Application

T-Connector

General

Color Code - Side A	Green
Color Code - Side B	Green
Connector Type	T-COUPLER
Die Index	11/11
Die Index Run Side	11
Die Index Tap Side	11
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810198490
UPC 12 Digit	7818101984900

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	95 mm
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.75 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Width inch	1.61 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	1 AWG
Conductor - Copper Str Run Range	1 AWG
Conductor - Copper Str Tap	1 AWG
Conductor - Copper Str Tap Range	1 AWG
Conductor - Material	COPPER
Conductor Size	1 AWG-1 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	11600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YST_LineArt](#)
[Sales Drawings - 1007470001_D](#)



A proud member of the Hubbell Family.

