



Compresson T-Connector

By Burndy
Catalog # YST3131



UNINSULATED HIGH VOLTAGE COPPER COMPRESSION
SPLICE STANDARD BARREL-TAPERED ENDS.

Application

T-Connector

General

Color Code	Red
Color Code - Side A	Red
Color Code - Side B	Red
Connector Type	T-COUPLER
Die Index	18/18
Die Index Run Side	18
Die Index Tap Side	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810502051
UPC 12 Digit	7818105020511

Dimensions

Dimension - A Outside Diameter inch	0.88 in
Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - B Outside Diameter inch	0.88 in
Dimension - Height inch	3.12 in
Dimension - L Length Overall mm	140 mm
Dimension - Length BB inch	2.25 in
Dimension - Length Overall inch	5.50 in
Dimension - Width inch	2.25 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	350 KCMIL
Conductor - Copper Str Run Range	350 kcmil
Conductor - Copper Str Tap	350 KCMIL
Conductor - Copper Str Tap Range	350 kcmil
Conductor - Material	COPPER
Conductor Size	350 KCMIL-350 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2960

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YST_LineArt](#)
[Sales Drawings - 2388613](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YST3131-SPEC-EN | REV 5/2024

