



Compresson T-Connector

By Burndy
Catalog # YST3939



UNINSULATED HIGH VOLTAGE COPPER COMPRESSION
SPLICE STANDARD BARREL-TAPERED ENDS.

Application

T-Connector

General

Color Code	Black
Color Code - Side A	Black
Color Code - Side B	Black
Connector Type	T-COUPLER
Die Index	24/24
Die Index Run Side	24
Die Index Tap Side	24
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810116814
UPC 12 Digit	7818101168144

Dimensions

Dimension - A Outside Diameter inch	1.30 in
Dimension - B Length fraction	2-7/8 in
Dimension - B Length inch	2.88 in
Dimension - B Outside Diameter inch	1.30 in
Dimension - Height inch	4.64 in
Dimension - L Length Overall mm	206 mm
Dimension - Length BB inch	3.34 in
Dimension - Length Overall inch	8.12 in
Dimension - Width inch	3.34 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	750 KCMIL
Conductor - Copper Str Run Range	750 kcmil
Conductor - Copper Str Tap	750 KCMIL
Conductor - Copper Str Tap Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL-750 KCMIL
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	12
Minimum Pack Quantity	12
Pallet Quantity	1080

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 2388619](#)



A proud member of the Hubbell Family.

