

## Uninsulated Splice For 12 - 10 AWG

By Burndy  
Catalog # YSV10

Copper Butt Splice, w/ Inspection Hole, 12-10 AWG, 0.75" Splice Length, Tin Plated.



### Application

For All Heavy Duty Industrial And General Purpose Applications

### General

Connector Type	Seamless Butt Splice
Die Index	36
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	Splice
UPC	781810806050
UPC 12 Digit	7818108060500

### Dimensions

Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.31 in
Dimension - Inside Diameter inch	0.13 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	5/16

### Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

### Conductor Related

Conductor - Copper Solid Size	12;11;10
Conductor - Copper Solid Size Range	12-10
Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Navy Size	6 (7);6 (19);9 (7);9 (37)
Conductor - Copper Str Navy Size Range	6 (7)-9 (37)
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> <li>• CU C Str Aircraft-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094197](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YSV10-SPEC-EN | REV 8/2023