



# YSV14HBOX, Uninsulated Splice For 16 - 14 AWG

By Burndy  
Catalog # [YSV14HBOX](#)

Uninsulated Splice For 16 - 14 AWG.



## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

## Application

For All Heavy Duty Industrial And General Purpose Applications

## General

Catalog Number	YSV14HBOX
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810534502

## Dimensions

Cable Insulation Diameter Maximum	0.15 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Strip Length inch	1/4 in

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor - Copper Solid Size	20;18;17;16;15;14;13;12
Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14;AN 12
Conductor - Copper Str Size	22;20;18;16;14
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> <li>• CU C Str Aircraft-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_KFFYSVH\\_LineArt](#)
- [Sales Drawings - 50094199](#)



A Hubbell brand