



Uninsulated Splice For 22 - 18 AWG (Nickel Plated)

By Burndy
Catalog # [YSV18NK](#)



Uninsulated Splice For 22 - 18 AWG (Nickel Plated).

General

Connector Type	Seamless Butt Splice
Die Index	36
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	HYLINK™
Type	Splice
UPC	781810269824
UPC 12 Digit	7818102698244

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Inside Diameter inch	0.06 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Strip Length inch	1/4

Electrical Ratings

Voltage - Maximum	35000 V
-------------------	---------

Conductor Related

Conductor - Copper Solid Size	20;18
Conductor - Copper Solid Size Range	20-18
Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Navy Size	1 (1);1 (7);1 (10);1 1/2 (1);1 1/2 (7);1 1/2 (16);1 1/2 (41);2 (7);2 1/2 (1);2 1/2 (19);2 1/2 (26)
Conductor - Copper Str Navy Size Range	1 (1)-2 1/2 (26)
Conductor - Copper Str Size	22;20;18
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YSV18NK-SPEC-EN | REV 8/2023

