



Compression Splice

By Burndy
Catalog # YSV25FX

1/0 Flex G,H,I,K,M,DLO, 1/0 AWG AWG CU, Long Barrel,
Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Pink
Color Code, 12 Die Index.



Application

Wire Splice

General

Color Code	Pink
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	12
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSV
UPC	621945621473

Dimensions

Dimension - B Length inch	1.45
Length	3.29 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - Burndy_Copper Flex Splices - Long Barrel_Brochure](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.

