



# Uninsulated Splice For 1/0 AWG

By Burndy  
Catalog # [YSV25L](#)

HYLINK™ Uninsulated Compression Butt Splice; Seamless Standard Barrel; Accommodates: 1/0 AWG Str/Sol, AN, Aircraft; Length: 1.53" ; 600 V Max; Bulk Package



## Application

For Aircraft, Light Duty Industrial And General Purpose Applications

## General

Connector Type	Seamless Butt Splice
Die Index	43
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810543931

## Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.53 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Strip Length inch	11/16 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Str Aircraft Size	AN 0
Conductor - Copper Str Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li><li>• CU C Str Aircraft-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	46400

## Product Assets

[3D Models - YSV25L\\_MODEL-PDF](#)  
[3D Models - YSV25L\\_MODEL-STEP](#)  
[3D Models - YSV25L\\_MODEL-IGES](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094198](#)



A proud member of the Hubbell Family.