



Compression Splice

By Burndy
Catalog # [YSV27FX](#)

3/0 Flex G,H,I,K,M,DLO, 3/0 AWG AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Orange Color Code, 14 Die Index.



Application

Wire Splice

General

Color Code	Orange
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	14
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSV
UPC	621945621497

Dimensions

Dimension - B Length inch	1.45
Length	3.29 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper DLO Size Range	3/0 AWG
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex H Size Range	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Brochures - Burndy_Copper Flex Splices - Long Barrel_Brochure](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.

