



# Compression Splice

By Burndy  
Catalog # [YSV2CFX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.



## Application

Wire Splice

## General

Color Code	Brown
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	10
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSV
UPC	621945624061

## Dimensions

Dimension - B Length inch	1.34
Length	3.06 in

## Electrical Ratings

Voltage Rating	35 kV
----------------	-------

## Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

## Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

- [Brochures - Burndy\\_Copper Flex Splices - Long Barrel\\_Brochure](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.

