



Compression Splice

By Burndy
Catalog # [YSV3CFX](#)

3 Flex G,H,I,K,M,DLO, 3 AWG AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, White Color Code, 9 Die Index.



Application

Wire Splice

General

Color Code	White
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	9
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSV
UPC	621945624054

Dimensions

Dimension - B Length inch	1.21
Length	2.81 in

Electrical Ratings

Voltage Rating	35 kV
----------------	-------

Conductor Related

Conductor - Copper DLO Size	3 AWG
Conductor - Copper DLO Size Range	3 AWG
Conductor - Copper Flex G Size	3 AWG
Conductor - Copper Flex G Size Range	3 AWG
Conductor - Copper Flex H Size	3 AWG
Conductor - Copper Flex H Size Range	3 AWG
Conductor - Copper Flex I Size	3 AWG
Conductor - Copper Flex I Size Range	3 AWG
Conductor - Copper Flex K Size	3 AWG
Conductor - Copper Flex K Size Range	3 AWG
Conductor - Copper Flex M Size	3 AWG
Conductor - Copper Solid Size Range	2 Sol
Conductor - Copper Str Size	3 AWG
Conductor - Material	COPPER
Conductor Size	3 AWG
Conductor Type	CODE/FLEX
Wire Size	3 AWG

Certifications And Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Brochures - Burndy_Copper Flex Splices - Long Barrel_Brochure](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50117138](#)





A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSV3CFX-SPEC-EN | REV 5/2024