



# Compression Splice

By Burndy  
Catalog # YSV4CFX

4 Flex G,H,I,K,M,DLO, 4 AWG AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gray Color Code, 8 Die Index.



### Application

Wire Splice

### General

Color Code	Gray
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	8
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSV
UPC	621945624047

### Dimensions

Dimension - B Length inch	1.21
Length	2.79 in

### Electrical Ratings

Voltage Rating	35 kV
----------------	-------

### Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

### Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

- [Brochures - Burndy\\_Copper Flex Splices - Long Barrel\\_Brochure](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.

