



## Compression Splice

By Burndy  
Catalog # [YSV6CFX](#)

6 Flex G,H,I,K,M,DLO, 6 AWG AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 7 Die Index.



### Application

Wire Splice

### General

Color Code	Blue
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	7
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSV
UPC	621945624030

### Dimensions

Dimension - B Length inch	1.09
Length	2.53 in

### Electrical Ratings

Voltage Rating	35 kV
----------------	-------

### Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Solid Size Range	6 Sol
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

### Certifications and Compliance

Certification - CSA Approved	CSA
Certification - cULus	NO
Industry Standard(s)	UL 486A-486B

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Brochures - Burndy\\_Copper Flex Splices - Long Barrel\\_Brochure](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50117138](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YSV6CFX-SPEC-EN | REV 1/2024