



## Uninsulated Splice For 6 AWG

By Burndy  
Catalog # YSV6CLBOX

HYLINK™ Uninsulated Compression Butt Splice; Seamless Standard Barrel; Accommodates: #6 AWG Str/Sol, AN, Aircraft; Length: 1.12" ; 600 V Max



### Application

For Aircraft, Light Duty Industrial And General Purpose Applications

### General

Connector Type	Seamless Butt Splice
Die Index	39
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810534700

### Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.12 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	5/8 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6 AWG
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li><li>• CU C Str Aircraft-Size</li></ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094198](#)



A proud member of the Hubbell Family.