



Uninsulated Splice For 8 AWG

By Burndy
Catalog # YSV8CLBOX

HYLINK™ Uninsulated Compression Butt Splice; Seamless Standard Barrel; Accommodates: #8 AWG Str/Sol, AN, Aircraft; Length: 1" ; 600 V Max



Application

For Aircraft, Light Duty Industrial And General Purpose Applications

General

Connector Type	Seamless Butt Splice
Die Index	38
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810543504

Dimensions

Dimension - B Length fraction	4/9 in
Dimension - B Length inch	0.44 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Strip Length inch	7/16 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_KFFYSVL_LineArt](#)
[Sales Drawings - 50094198](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YSV8CLBOX-SPEC-EN | REV 5/2024