



YTS32R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # YTS32R



Aluminum outer sleeve for full tension splice kit, 336.4 Kcmil, 717 Index, Outer sleeve for Hysplices provides gradual transition of stress.

General

Catalog Number	YTS32R
Connector Type	Splice
Die Index	717
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810000526
UPC 12 Digit	7818100005266

Dimensions

Dimension - L Length Overall mm	439.4
Dimension - Length Overall inch	17.3

Conductor Related

Conductor - ACSR Str Size	336.4 (24/7) Widgeon Kcmil; 336.4 (26/7) Linnet Kcmil; 336.4 (30/7) Oriole Kcmil
Conductor - AL Str Size	336 kcmil
Conductor - AL Str Size Range	336 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	768

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE058062-01](#)
- [Specifications - YTS32R](#)



A Hubbell brand