



YTS351AT, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS351AT](#)



Full Tension Splice for Stranded Aluminum Transmission Line.

General

Connector Type	Splice
Die Index	720
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810515457
UPC 12 Digit	7818105154577

Dimensions

Dimension - B Length fraction	5-13/16 in
Dimension - B Length inch	5.82 in
Dimension - L Length Overall mm	302 mm
Dimension - Length Overall inch	11.88 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - AL Str Size	500 (37) Hyacinth Kcmil; 556.5 (19) Dahlia Kcmil; 556.5 (37) Mistletoe Kcmil
-------------------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	2016

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD061865-01](#)



A proud member of the Hubbell Family.