



YTS361A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS361A](#)



Aluminum full tension HYSPLICE™, 600-636 Kcmil, 722 Index.

General

Connector Type	Splice
Die Index	722
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810129203
UPC 12 Digit	7818101292033

Dimensions

Dimension - L Length Overall mm	308 mm
Dimension - Length Overall inch	12.14 in

Conductor Related

Conductor - AL Str Size	600 kcmil;636 kcmil
Conductor - AL Str Size Range	600 kcmil-636 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus™	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1512

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD061864-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTS361A-SPEC-EN | REV 8/2023