



YTS36R36RSHT, High Temperature Splice

By Burndy
Catalog # [YTS36R36RSHT](#)



Compression High Temperature Splice.

General

Connector Type	Deadend
Die Index	720
Material	Aluminum
UPC	781810484081
UPC 12 Digit	7818104840811

Dimensions

Dimension - B Length inch	12.93 in
Dimension - L Length Overall mm	664 mm
Dimension - Length Overall inch	26.16 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - ACSS Str Size	477 (24/7) kcmil;477 (26/7) kcmil
Conductor - ACSS Str Size Range	477 (24/7) kcmil-477 (26/7) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YTS-R-RSHT_LINEART_BW](#)
[Sales Drawings - 50018588](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YTS36R36RSHT-SPEC-EN | REV 5/2024