



YTS391A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS391A](#)



Al Tube Full Tension Splice, 795 kcmil Al, 37 Str, 795 kcmil Al, 61 Str, 800 kcmil Al, 61 Str, 15.81" L, For Stranded Al Cable.

General

Connector Type	Splice
Die Index	724
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016220
UPC 12 Digit	7818100162200

Dimensions

Dimension - L Length Overall mm	402 mm
Dimension - Length Overall inch	15.81 in

Conductor Related

Conductor - AL Str Size	795 (37, 61) Kcmil; 800 (61) Kcmil
-------------------------	------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	960

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD061864-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTS391A-SPEC-EN | REV 8/2023