



YTS391AT, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS391AT](#)



Al Tube Full Tension Splice, EHV, 795 - 800 kcmil Al, 16.36" L, 724 Index.

General

Connector Type	Splice
Die Index	724
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016244
UPC 12 Digit	7818100162444

Dimensions

Dimension - L Length Overall mm	416 mm
Dimension - Length Overall inch	16.36 in
Dimension - Outside Diameter inch	1.61

Conductor Related

Conductor - AL Str Size	795 kcmil;800 kcmil
Conductor - AL Str Size Range	795 kcmil-800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	960

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD061865-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTS391AT-SPEC-EN | REV 8/2023