



# YTS39A, ACSR - Full Tension Compression Splice

By Burndy  
Catalog # [YTS39A](#)



Al Tube Full Tension Splice, 715.5, 750 kcmil Al, 230 kV, 13.36" L, 724 Index.

## General

Connector Type	Splice
Die Index	724
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016169
UPC 12 Digit	7818100161699

## Dimensions

Dimension - L Length Overall mm	339 mm
Dimension - Length Overall inch	13.36 in

## Conductor Related

Conductor - AL Str Size	715.5 (37, 61) Kcmil; 750 (61) Kcmil
-------------------------	--------------------------------------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD061864-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YTS39A-SPEC-EN | REV 8/2023