



# YTS39R43RS, ACSR - Full Tension Compression Splice

By Burndy  
Catalog # [YTS39R43RS](#)



Full Tension Splice Kit for ACSR Conductor.

### General

Catalog Number	YTS39R43RS
Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810209462
UPC 14 Digit GTIN	00781810209462

### Dimensions

Dimension - B Length inch	2.47 in
Dimension - L Length Overall mm	505 mm
Dimension - Length Overall inch	19.88 in
Dimension - Outside Diameter inch	1.50 in

### Conductor Related

Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	480

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YTS-R-RS\\_LINEART\\_BW](#)
- [Sales Drawings - SE058062-01](#)
- [Specifications - YTS39R43RS](#)