



YTS431AT, Aluminum Full Tension Splice

By Burndy
Catalog # [YTS431AT](#)



Al Full Tension Splice For Stranded Aluminum Transmission Line, 874.5 kcmil, 954 kcmil, 345 kV, 725 Index, Extra High Voltage Applications.

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810055298
UPC 12 Digit	7818100552988

Dimensions

Dimension - L Length Overall mm	455 mm
Dimension - Length Overall inch	17.92 in

Conductor Related

Conductor - AL Str Size	874.5 (37, 61) Kcmil - 954 (37, 61) Kcmil
Conductor - AL Str Size Range	874.5 Kcmil-954 Kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	8
Minimum Pack Quantity	8
Pallet Quantity	768

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD061865-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTS431AT-SPEC-EN | REV 8/2023