



YTS451R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS451R](#)



Full Tension Two-piece Splice, Al Sleeve, 715.5kcmil-795kcmil
ACSR, 250 kV, 28.96" L, 725 Index.

General

Catalog Number	YTS451R
Connector Type	Splice
Die Index	725
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016299
UPC 14 Digit GTIN	00781810016299

Dimensions

Dimension - L Length Overall mm	735.6 mm
Dimension - Length Overall inch	28.96 in

Conductor Related

Conductor - ACSR Str Size	715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil
---------------------------	--

Conductor - ACSR Str Size Range	715.5 (54/7) Crow kcmil-795 (26/7) Drake kcmil
------------------------------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	280

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YTS-A_LineArt](#)
- [Sales Drawings - SE058062-01](#)
- [Specifications - YTS451R](#)



A Hubbell brand