



YTS48AT, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS48AT](#)



Al Full Tension Splice For Stranded Aluminum Transmission Line, 2000 kcmil, 345 kV, 735 Index, Extra High Voltage Applications.

General

Connector Type	Splice
Die Index	735
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810183106
UPC 12 Digit	7818101831066

Dimensions

Dimension - L Length Overall mm	585 mm
Dimension - Length Overall inch	23.02 in

Conductor Related

Conductor - AL Str Size	2000 kcmil
-------------------------	------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	240

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD061865-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTS48AT-SPEC-EN | REV 8/2023