



YTS48R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS48R](#)



Al Sleeve, 795, 900, 954 kcmil ACSR, 230 V, 29.16" L, 727 Index,
Included in Full Tension Splice.

General

Catalog Number	YTS48R
Connector Type	Splice
Die Index	727
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016275
UPC 12 Digit	7818100162755

Dimensions

Dimension - L Length Overall mm	740.7 mm
Dimension - Length Overall inch	29.16 in

Conductor Related

Conductor - ACSR Str Size	795 (30/19) Mallard Kcmil; 900 (45/7) Rubby; 954 (45/7) Rail Kcmil; 954 (54/7) Cardinal Kcmil
---------------------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	210

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YTS-A_LineArt](#)
- [Sales Drawings - SE058062-01](#)
- [Specifications - YTS48R](#)