



YTS48R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # YTS48R



Al Sleeve, 795, 900, 954 kcmil ACSR, 230 V, 29.16" L, 727 Index, Included in Full Tension Splice.

General

Catalog Number	YTS48R
Connector Type	Splice
Die Index	727
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016275
UPC 12 Digit	7818100162755

Dimensions

Dimension - L Length Overall mm	740.7 mm
Dimension - Length Overall inch	29.16 in

Conductor Related

Conductor - ACSR Str Size	795 (30/19) Mallard Kcmil; 900 (45/7) Rubby; 954 (45/7) Rail Kcmil; 954 (54/7) Cardinal Kcmil
---------------------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	210

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YTS-A_LineArt](#)
- [Sales Drawings - SE058062-01](#)
- [Specifications - YTS48R](#)



A Hubbell brand