



YTS48RT481RS, Full Tension Splice Kit for ACSR EHV

By Burndy
Catalog # [YTS48RT481RS](#)



Full Tension Splice Kit for ACSR Conductor EHV.

General

Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810222003
UPC 12 Digit	7818102220033

Dimensions

Dimension - L Length Overall mm	741 mm
Dimension - Length Overall inch	29.16 in
Dimension - Outside Diameter inch	1.97 in

Conductor Related

Conductor - ACSR Str Size	900 (45/7) Ruddy Kcmil; 954 (45/7) Rail Kcmil
---------------------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	140

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YTS-RT-RS_LINEART_BW](#)
[Sales Drawings - SE058062](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YTS48RT481RS-SPEC-EN | REV 5/2024