



YTS49R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS49R](#)

Aluminum Sleeve, 1033.5 - 1113 Kcmil ACSR, 230 V, 29.02" L,
727 Index, Included in Full Tension Splice.



General

Connector Type	Splice
Die Index	727
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016114
UPC 12 Digit	7818100161144

Dimensions

Dimension - L Length Overall mm	737.1 mm
Dimension - Length Overall inch	29.02 in

Conductor Related

Conductor - ACSR Str Size	1033.5 (45/7) Ortolan Kcmil; 1033.5 (54/7) Curlew Kcmil; 1113 (45/7) Bluejay Kcmil
---------------------------	--

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	105

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YTS-A_LineArt](#)
[Sales Drawings - SE058062-01](#)



A proud member of the Hubbell Family.