



YTS49RT48RSHT, Full Tension ACSS EHV Splice Kit

By Burndy
Catalog # [YTS49RT48RSHT](#)

Full Tension ACSS EHV Splice Kits, YTS49RTHT Aluminium Sleeve (Qty. 1), YTS48RS Steel Sleeve (Qty. 1), CURLEW 1033.5 (54/7) kcmil.



Application

For ACSS Conductor, Corona free operation up to 550 KV

General

Connector Type	Splice
Die Index	727;726
Die Type	L727 for Aluminium Sleeve, L726 Steel Sleeve
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810501368
UPC 12 Digit	7818105013688

Dimensions

Dimension - B Length inch	4.00 in
Dimension - Length Overall inch	37.02 in
Dimension - Outside Diameter inch	1.97 in

Electrical Ratings

Voltage - Maximum	550 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	CURLEW 1033.5 (54/7) kcmil
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	200

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10092589](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YTS49RT48RSHT-SPEC-EN | REV 8/2023