



YTS549RT549RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS549RT549RS](#)



Full Tension Splice Kit for ACSR Conductor EHV.

General

Catalog Number	YTS549RT549RS
Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810222102
UPC 14 Digit GTIN	00781810222102

Dimensions

Dimension - L Length Overall mm	867 mm
Dimension - Length Overall inch	34.13 in
Dimension - Outside Diameter inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	1590 (45/7) Lapwing kcmil
Conductor - ACSR Str Size Range	1590 (45/7) Lapwing kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YTS-RT-RS_LINEART_BW](#)
- [Sales Drawings - SE058062](#)
- [Specifications - YTS549RT549RS](#)