



YTS59RT59RS, Full Tension Splice Kit for ACSR EHV

By Burndy
Catalog # [YTS59RT59RS](#)



Full Tension Splice Kit for ACSR Conductor EHV.

General

Connector Type	Splice
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810238912
UPC 12 Digit	7818102389122

Dimensions

Dimension - L Length Overall mm	1090 mm
Dimension - Length Overall inch	42.91 in
Dimension - Outside Diameter inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil
---------------------------	-----------------------------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	120

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YTS-RT-RS_LINEART_BW](#)
[Sales Drawings - SE058062](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YTS59RT59RS-SPEC-EN | REV 5/2024