



YTS59RT59RSHT, Full Tension ACSS EHV Splice Kit

By Burndy
Catalog # YTS59RT59RSHT



Full Tension ACSS EHV Splice Kits, YTS59RTHT Aluminium Sleeve (Qty. 1), YTS59RS Steel Sleeve (Qty. 1), BLUEBIRD 2156 (84/19) kcmil.

Application

For ACSS Conductor, Corona free operation up to 550 kV

General

Catalog Number	YTS59RT59RSHT
Connector Type	Splice
Die Index	735;726
Die Type	L735 for Aluminium Sleeve, L726 Steel Sleeve
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810516034
UPC 12 Digit	7818105160344

Dimensions

Dimension - B Length inch	4.07 in
Dimension - Length Overall inch	50.91 in
Dimension - Outside Diameter inch	2.50 in

Electrical Ratings

Voltage - Maximum	550 kV
-------------------	--------

Conductor Related

Conductor - ACSS Str Size	BLUEBIRD 2156 (84/19) kcmil
Conductor - Material	Aluminum

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10092589](#)
[Specifications - YTS59RT59RSHT](#)



A Hubbell brand