



# YTU25R2R, Aluminum T-Tap Connector

By Burndy  
Catalog # [YTU25R2R](#)



Al Compression T-Tap Connector, 1/0 AWG ACSR/Al/Cu(Run), #2 Str ACSR/Al/Cu(Tap).

## General

Connector Type	Tap
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810124642
UPC 12 Digit	7818101246422

## Dimensions

Dimension - B Length inch	0.82 in
Dimension - Height inch	2.40 in
Dimension - L Length Overall mm	123 mm
Dimension - Length Overall inch	4.84 in

## Conductor Related

Conductor - ACSR Str Run	1/0 AWG
Conductor - ACSR Str Tap	2 AWG(6-1,7-1 STR)
Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Tap	2 AWG STR
Conductor - Copper Str Run	80 kcmil
Conductor - Copper Str Tap	2 AWG(7,8 STR)

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD031286](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YTU25R2R-SPEC-EN | REV 8/2023