

YTU27R27R, 1-piece Heavy-Wall Aluminum Tap Connector

By Burndy
Catalog # [YTU27R27R](#)



1-piece heavy wall AL compression tap connector for secondary service drop and transformer tap to primary or secondary, 3-3/8 IN Height.

General

Catalog Number	YTU27R27R
Connector Type	Tap
Die Index Run Side	L
Die Index Tap Side	L
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810155455
UPC 12 Digit	7818101554555

Dimensions

Dimension - B Length inch	1.88 in
Dimension - Height inch	3.32 in
Dimension - L Length Overall mm	178 mm
Dimension - Length Overall inch	7 in

Conductor Related

Conductor - ACSR Str Run	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Tap	3/0 (6/1) Pigeon AWG
Conductor - AL Str Run	3/0 AWG
Conductor - AL Str Tap	3/0 AWG
Conductor - Copper Str Run	3/0 AWG
Conductor - Copper Str Tap	3/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [3D Models - YTU27R27R_MODEL-STEP](#)
- [3D Models - YTU27R27R_MODEL-IGES](#)
- [3D Models - YTU27R27R_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YTU-R-R_LineArt](#)
- [Sales Drawings - SD031286](#)
- [Specifications - YTU27R27R](#)